

SECTIONS
06 41 00 * 10 50 00
CUSTOM WOOD VENEER ATHLETIC LOCKERS

PART 1, GENERAL

1.1 SECTION INCLUDES

- A. Custom Wood Veneer Athletic Lockers and accessories.

1.2 REFERENCES

- A. Architectural Woodwork Institute: AWI - Quality Standards Illustrated.

1.3 SUBMITTALS

- A. Product Data: Available upon request, including:
 - 1. Preparation instructions and recommendations.
 - 2. Storage and handling requirements and recommendations.
 - 3. Installation methods.
 - 4. Product data specific to materials used in construction of locker.
- B. Shop Drawings: Indicate locker plan layout for Hollman contracted installations, component profiles and elevations, schedule of finishes, and accessories.

1.4 QUALITY ASSURANCE

- A. Perform work in accordance with AWI (Architectural Woodwork Institute) Architectural Woodwork Quality Standards Illustrated.
- B. Woodwork Fabricator Certification: Certified **"PREMIUM"** participant in AWI's Quality Certification Program or licensee of WI's Certified Compliance Program.
- C. Manufacturer/Fabricator Qualifications: Manufacturer/fabricator with not less than 5 years experience with successful production of products and systems similar to scope of this Project, with a record of successful in-service performance and completion of projects for a period of not less than 5 years, and with sufficient production capability, facilities, and personnel to produce required Work.
- D. Warranted to be free from any major structural defects attributable to the manufacturing process under normal use and service for a period of (3) Years from the date of delivery.

1.5 DELIVERY, STORAGE, AND HANDLING

- A. Store products in a dry, ventilated area until ready for installation.
- B. Protect finishes from moisture, soiling and damage during handling.

1.6 PROJECT CONDITIONS

- A. Maintain environmental conditions (temperature, humidity, and ventilation) within limits recommended by manufacturer for optimum results. Do not install products under environmental conditions outside manufacturer's absolute limits.
- B. During and after installation, maintain same temperature and humidity conditions in building spaces as will occur after occupancy.
- C. Protect locker finish and adjacent surfaces from damage.

PART 2 , PRODUCTS

2.1 MANUFACTURERS

- A. Hollman Inc. - 1825 Walnut Hill Lane, Irving, TX 75038, Toll Free (800) 433-3630, Phone (972) 815-4000, Fax (972) 815-2921, Email: lockers@hollman.com.
- B. Substitutions: Not permitted.
- C. Requests for substitutions will be considered in accordance with provisions of Section 01600.

2.2 LOCKERS

- A. Locker Frame: Wood veneer ¾ inch A Grade plain sliced veneer on MDF core, wood species and finish listed below.
 - 1. Typical Wood Species: Maple, Red Oak, Cherry, Walnut, Mahogany or as indicated.
- B. Locker Edges: All exposed edges of locker are edge banded using either of the below methods, or a combination thereof.
 - 1. Wood veneer edge banded with matching wood species and finish to the rest of the locker
 - 2. 22 gauge stainless steel cap (typically used with front-facing exposed edges)
- C. Stain Finish: Stain choices include Clear, Amber, Hazelnut, Chestnut, Pecan, Coffee Bean, Espresso, or a custom-formulated project-specific finish.
- D. Wood Finish: All wood surfaces are sealed with 100% solid UV cured sealer, with less than 1% Volatile Organic Compounds (VOCs) and then finished with a water-borne UV cured clear anti-microbial topcoat, with less than 1% VOCs, applied in the desired sheen (10, 35, or 50 degrees).
- E. Door Styles: Doors and drawer fronts can be customized to maximize design impact
 - 1. Shaker style door insert options listed below:
 - a. 3/16 inch veneer with matching wood species and finish to the rest of the locker
 - b. ¼ inch clear or frosted glass
 - c. ¼ inch clear or frosted glass with logo
 - d. Colored glass
 - e. Metal grill
 - 2. Flush Veneer

Hollman Wood Athletic
Locker Specifications

- F. Bottom Unit: Functions as storage and seating as indicated on project drawings. The two standard configurations are as follows:
 - 1. Integrated pull out drawer unit with metal grill for ventilation
 - 2. Integrated storage bin topped with lift-up seat with soft-close hinges

- G. Seating: Seating areas will be topped with one of the following:
 - 1. ACQUA Leather covered cushion with or without embossed logo available: Breathable leather, test proven to repel water (sweat), bacteria, and resist noticeable staining
 - 2. Industrial Marine Grade Vinyl covered cushion with or without screen printed logo available
 - 3. Wood Veneer finished to match locker interior with solid bull nose edge
- H. Hardware:
 - 1. Hinges: Samet European concealed hinge
 - 2. Optional Soft close mechanisms: Used in bench seats and Upper lift up doors.
 - a. Sugatsune heavy-duty soft close (Part number: HDS-20)
 - b. Hafele Maxi Lid System
 - 3. Locks: Available with standard or upgraded options
 - a. Standard option 1: Padlock hasp
 - b. Standard option 2: Heavy-duty five-pin tumbler key lock, furnished with 2 master keys and 2 user keys per lock
 - c. Upgraded option 1: High-security stainless steel padlock hasp
 - d. Upgraded option 2: Keyless Security Lock, available in brushed satin or white gloss
 - e. Upgraded option 3: Built-in combination lock
 - f. Upgraded option 4: Digilock ATS & APS (with or without pull)
 - g. Upgraded option 5: Ojmar OCS card lock
 - 4. Drawer Glides: Full extension, side mounted, cold rolled steel material, and 150 lbs load capacity each
- I. Accessories:
 - 1. Metal Grills: Generally inset into doors and drawers, options available include:
 - a. Type 304 16-gauge stainless steel with 3/16-inch round perforations at 5/16 inch center
 - b. Brushed aluminum perforated metal grill
 - c. Project-specific customization available (colors, shapes, design)
 - 2. Name Plate Holder: 2x12 inch or 2x18 inch brushed chrome with blank insert standard with custom sizes available.
 - 3. Coat Rods: 1 inch diameter, chrome finish
 - 4. Coat Hooks:
 - a. Standard option: Hafele traditional style coat hook, part number: 885.06.209
 - b. Athletic option: Hollman custom made 14 gauge Stainless Steel "U" hook.
 - c. Premium option: Doug Mockett coat hook
 - 5. Drawer/Door Pulls: Hafele
 - 6. Valence: Various heights finished to match the lockers
- J. Lighting: LED lights for locker top or integrated within locker body. Accent color lights are also available. Electrical wiring to be coordinated with a certified electrician during installation.

Hollman Wood Athletic
Locker Specifications

- K. Electric Outlets & USB Docks: Integrated Electrical outlet and USB outlets built into locker interiors to allow charging of electronics.
- L. Venting: Fans, metal grill at specific locations to provide free air flow.

2.3 FABRICATION

- A. Lockers shall be fabricated using doweled and glued & screwed assembly process.
- B. Fabricate lockers square, rigid and without warp, with the finished faces flat and free of scratches and chips.
- C. Machine all parts and attachment holes accurately and without chips and defects.

PART 3, EXECUTION

3.1 EXAMINATION

- A. Do not begin installation until adjacent substrates and finishes have been properly prepared.
- B. Verify prepared bases are in correct position and configuration.
- C. If preparation is the responsibility of another installer, notify Architect of unsatisfactory preparation before proceeding.

3.2 PREPARATION

- A. Clean surfaces thoroughly prior to installation.
- B. Prepare surfaces using the methods recommended by the manufacturer for achieving the best result for the substrate under the project conditions.
- C. Verify adequacy of backing and support framing.

3.3 INSTALLATION

- A. Install in accordance with manufacturer's instructions.
- B. If Hollman is not contracted for installation, client must unload lockers from the delivery truck.
- C. Place and secure on prepared base.
- D. Secure lockers with anchor devices to suit substrate materials. Minimum Pullout Force: 100 lb (445 N).
- E. Install end panels, filler panels, tops and bases as indicated on the approved shop drawings.
- F. Install accessories.
- G. Set and secure lockers in place; rigid, plumb, and level.
- H. Use concealed joint fasteners to align and secure adjoining cabinet units.
- I. Conceal screw heads with plastic caps to match locker interior.

3.4 ADJUSTING

- A. Adjust moving or operating parts to function smoothly and correctly.

3.5 CLEANING

Hollman Wood Athletic
Locker Specifications

- A. Clean locker interiors and exterior surfaces.

3.6 PROTECTION

- A. Protect installed products until completion of project.
- B. Touch-up, repair or replace damaged products before Substantial Completion.